

# LASER DIODE INTENSITY MODULATION AND DEMODULATION TRAINER

OMEGATYPE FO-007A&B



**OMEGA TYPE FO-007A&B** Laser Diode Intensity Modulation and Demodulation Trainer has been developed to conduct studies on laser diode, optical fibres and optical communication methods, by signal transmission.

Practical experience on this Trainer carries great educative value for Science & Engineering Students.

### **OBJECTS:**

- 01 Characterisation of a Laser Diode.
  - Optical Power (Po) of a Laser Diode Vs Laser Diode Forward current (I<sub>F</sub>).
  - 1.2 Monitor Photo diode Current (I<sub>M</sub>) Vs Laser Optical Power Output (Po).
- O2 Study of Automatic Current Control (ACC) or Automatic Power Control (APC) Modes of Operation
  - 2.1 Comparison of ACC and APC Modes of Operation.
- 03 Design and Evaluation of an Laser Diode (LD) Analog I, System
  - Vo Vs Vin at Specified Optical Carrier Power Levels, Po.
  - 3.2 Determination of Vin (max) at Specified Po for Distortion-free Vo.
- Design and Evaluation of Laser Diode LD Digital Transmission System
  - 4.1 Rise time and Fall time Pulse width Distortions and Determination of Propagation Delay.
- 05 Transmission of Laser Through an Optical Fibre
  - 5.1 To measure loss in dB of Step-index Multimode plastic Fibre Patchcord.
  - 5.2 To measure loss in dB of Graded-Index, Multimode Glass Fibre Patchcord.
  - 5.3 To measure loss in dB of Two Patchcords connected by the in-line adaptor.
- 06 Laser Free Space Communication
  - 6.1 Analogue Free Space Communication System.
  - 6.2 Digital Free Space Communication System.
- 07 Determination of Numerical Aperature of PMMA Fibre Cable

#### **FEATURES**

The trainer consists of the following built-in parts.

- 01 Laser Diode Transmitter unit having following built-in parts OMEGATYPE FO-001A
  - 1.1 Laser Diode transmitter module.
  - 1.2 6V DC at 100mA, IC Regulated Power Supply internally connected.
  - 1.3 SPDT switch to select Automatic Current Control (ACC) or Automatic Power Control (APC).
  - 1.4 Potentiometer to set power output.
  - 1.5 Adequate no of other electronic components.
  - 1.6 Mains ON/OFF switch, Fuse and Jewel light.
- 02 Laser Diode Receiver unit having following built-in parts OMEGATYPE FO-007B.
  - 2.1 Laser Diode Receiver Module
  - 2.2 PIN Diode for measuring power of Laser Diode.
  - 2.3 Potentiometer to set voltage output.
  - 2.4 Adequate no. of other electronic components.
  - 2.5 6V DC at 100mA, IC Regulated Power Supply internally connected.
- 03 Two-metres PMMA Plastic Fibre patchcord (Cable-1).
- 04 Two-metres GI/mm Glass Fibre patchcord (Cable-2).
- 05 In-line SMA adaptor.
- 06 Numerical Aperature measurement Jig.
- 07 Mandrel.
- 08 Two 6V DC AT 100mA Adopter
- 09 The units are operative on 230V ±10% at 50Hz A.C. Mains.
- 10 Adequate no. of patch cords stackable 4mm spring loaded plug length 50cm.
- 11 Good Quality, reliable terminal/sockets are provided at appropriate places on panel for connections / observation of waveforms.
- 12 Strongly supported by detailed Operating Instructions, giving details of Object, Theory, Design procedures, Report Suggestions and Book References.

## OTHER APPARATUS REQUIRED:

- 01 AF/RF Generator 10Hz to 1 MHz OMEGATYPE AO-309.
- 02 Three Digital Multimeter OMEGATYPE DMM-201.
- 03 Cathode Ray Oscilloscope 20MHz.

We are committed to the continuous development of our products, and therefore reserve the right to amend specifications without prior notice.

# **OMEGA ELECTRONICS**